

Features:

- **All-in-One Instrument -**
Measures, displays and stores voltage, decay time, temperature and humidity
- **Exceeds current requirements of ESD Assn. SP3.3 for Periodic Verification of Air Ionizers**
- **Test Balance and Decay**
- **Low Cost / Performance Ratio**
- **Hand-held, Battery Operated**
- **Microprocessor Driven**
- **Built-in Self Test**
- **Exclusive Monroe Electronics Two-year Warranty**

Operation


Model 287a performs manual or automatic decay and balance tests for periodic verification of ionization equipment. It then stores the results and averaged decay times for up to ten manual tests and up to ten complete automatic test sequences. Temperature and relative humidity are displayed real-time and recorded with the test data.

All instrument functions are controlled by four pushbuttons

In DECAY mode a built-in high voltage generator charges the plate to over 1050 volts. During testing the plate will discharge toward zero in the presence of ionization. The elapsed time of decay between 1000 volts and 100 volts is displayed.

In the BALANCE mode, isolated plate voltage, test duration and + and - peak voltages are displayed.

Self-tests include battery check and tests for functional errors.



Now take the mystery out of ionizer testing

Test your AC or DC room ionizers, laminar flow, overhead or benchtop ionizers or ionized compressed gas systems as simply as pushing a button.

Optional Model 287/22C 6" x 6" Plate Adapter

This optional adapter enables the model IPA 287a to perform very comparably to charged plate monitors designed to ESD Association standard No. 3.

Ionizer Performance Analyzer model 287a

Specifications:

Charger:	±1100volts, selectable polarity
Fieldmeter:	
Measurement Range	±1250V, 1V resolution
Accuracy	±5% of reading, ±2% typical
Zero Drift	<±4V in 90s, ±2V typical
Trip Points:	Fixed 1000V and 100V
Charge Plate:	1.7"x4" (≈10.6 inches periphery)
Capacitance	≈25pf
Self-discharge	<10% of full scale in 200s
Display:	2.4" x 0.63", 2 x 16 LCD
Timer	200.0s maximum, 0.1s resolution
Sensors:	±5% typ. from 10% to 90% RH
Humidity	@25°C
Temperature:	±2°C typical
Oper. Temp.:	25°C, ±10°C
Battery:	9 volt NEDA #1604A or equivalent alkaline (>40 hour life or >1300 charge cycles). Longer life may be achieved by using 9-volt lithium.
Dimensions:	8.1x4x1.9 inches (206 x 102 x 48 mm)
Weight:	1lb., 6oz. (0.63kg)

**Carrying Case
Included**

Calibration:

Monroe Electronics instruments are factory-calibrated prior to shipment. **Recalibration should be performed annually, or more frequently if specified by contract or company policy.** Your instrument should also be recalibrated any time it has been repaired or tampered with. We are happy to recalibrate your instrument for you at a reasonable cost, or provide information and procedures on calibration upon request.

Warranty:

Monroe Electronics, Inc., warrants that each instrument and sub-assembly manufactured by them shall be free from defects in material and workmanship for a period of two year after shipment from the factory. This warranty is applicable to the original purchaser only.

The finest Electrostatic instrumentation and support:

For more than 40 years - ever since we invented the feedback--nulled electrostatic voltmeter, Monroe has been the technology and quality leader in electrostatic detection and measurement instrumentation. Today we offer the world's most complete array of fieldmeters, voltmeters, and resistivity meters. Our customers include the leading makers of photocopiers and laser printers, converters and microelectronics worldwide.

We know you need quality support as well as quality products. We pride ourselves on providing our customers with the most knowledgeable applications and installation support — as well as superior customer service.

How can we help?

Contact your Monroe Electronics representative for price and delivery information on this and other ME products, to schedule a no-obligation demonstration at your convenience. For the name of your nearest dealer, or for technical or applications assistance, contact Monroe Electronics directly at the address and numbers below.

Verkauf und technische Betreuung

mem

Messtechnik & Elektronik GmbH
Pilartzstr. 9 D-83549 Eiselfing

Telefon: 08071 923060

FAX: 08071 9230619

mail@mem-gmbh.de

www.mem-gmbh.de

**ME MONROE
ELECTRONICS**